

# Slide Adapter 5x7 with Drop-in Plate



N°2 for M2  
lamature ø2.5

*Slide Adapter 5x7 with Hasselblad H attachment Drop-in Plate*

This new Sliding adapter is the product of our long experience in the manufacturing of professional cameras for high resolution digital photography. The stitching facility enables the photographer to almost double the file size of his image by shooting two images, side by side, and joining through software. This option gives the photographer many possibilities over the standard chip format and angle of view of lenses available

Completely re-designed with a new system of drop-in adapter plates and with further improved characteristics of the sliding movement and overall precision. The new drop-in system, allows the quick substitution of adapter plates; adapter plates are available for Hasselblad V, H and Mamiya 4,5x6 attachments. The digital back can be positioned either horizontally or vertically according to the needs.

The Silvestri standard 4 points fitting make it directly usable on our cameras: Bicam, S5 micron and T30 without any other accessory. There are also several adapter solutions for the most popular view cameras of other brands, by mean of interchangeable adapter plates or adapters integrated within the back.

Codice	Descrizione
D7023	Slide Adapter 5x7 with Silvestri Attachment (without Drop-in Plate)
D7023H	Drop-in Plate for Slide Adapter 5x7 Hasselblad 'H' type (for D7023)
D7023V	Drop-in Plate for Slide Adapter 5x7 Hasselblad 'V' type (for D7023)
D7023M	Drop-in Plate for Slide Adapter 5x7 Mamiya 645 AFD type (for D7023)

## Viewers



code **5030** Monocular reflex viewer  
for Stitching Sliding Adapter



code **5010** Magnifying glass  
in bellow for Stitching Sliding  
Adapter

Produced with CNC technology, the D7023 back has an extremely high precision and despite the complexity of a modular system, preserves the capability of using very short focal length lenses whilst still ensuring the accuracy.

In the picture on the right is underlined in the (01) position the unlocking element, by acting a slight pressure on it, the sliding element unlocks for passing from the viewing position to the shooting position:

- a) Central with horizontal framing
- b) Shifted 18,5mm to the right (shot 1) shifted 18,5mm to the left (shot 2). The two stitched shots will produce an image 49X72mm with the sensor placed in the vertical position ( diagonal 87mm.) While if the sensor is placed in the horizontal position a final image of 37X86mm will be produced; panoramic format ( diagonal 93mm.)



It is easy to see the advantages of this solution, the D7023 back substantially widens the possibility of use and the possible solutions.



In the image on the left side, you can notice the unlocking cursor of the Hasselblad H adapter plate (03) and the security button (02); to unlock the plate first press the security button (02) and move the cursor (03).

Image on the right:  
The unlocking of the Hasselblad H digital back is made on the back of the adapter plate. Slide the cursor (04) with the point of a pen and the digital back unlocks, perform the same operation to attach the digital back. Before completely removing the digital back make sure the cursor has moved back to its locking position.



**silvestri**

Via Della Gora 13/5 - 50025 Montespertoli FI, Italy  
e.mail [info@silvestricamera.com](mailto:info@silvestricamera.com) - [www.silvestricamera.com](http://www.silvestricamera.com)  
Tel +39.0571.675049 Fax +39.0571.675919